Burners

Laboratory Burners, Fuego SCS

For occasional or intermittent use, or serial flame sterilisation.

- Automatic gas ignition
- Low-profile easily cleaned stainless steel casing
- Gas and air regulators for fine control
- Visual alarm of burner head clogging and "burner hot" residual heat indicator
- Smooth sculpted design channels spillages away
- Can be tilted to avoid nozzle contamination
- Overheat protection system cuts off gas supply if overheating occurs or the electrical supply interrupted

Burner, Fuego SCS basic

With push-button ignition. The flame is maintained as long as the button is pressed and extinguishes on release. Alternatively, a foot pedal provided allows hands-free operation if required. Supplied with foot pedal, tilt mechanism, nozzles for natural gas or LPG, rack for up to 3 wire loop holders, tubing connector, wrench for gas connection and screwdriver for burner head. Overall 103 x 130 x 49mm L x W x H. Weight 0.7kg. Requires a 230V 50/60Hz single phase supply for the ignition circuit. Without gas supply. BY340-30 Fuego SCS basic

Burner, Fuego SCS

Generally as BY340-30 but without foot pedal and with Infra-red sensor, range 5 to 50mm, requiring two hand movements to activate the flame which is maintained for a timed period adjustable within two ranges: start-stop from 1 second to 2 hours or Auto-off from 1 second to 2 hours. An LCD readout with heat resistant glass face indicates time remaining and burner functions/ adjustment. An accessory foot pedal is available, if preferred. Requires a 230V 50/60Hz single phase supply for the ignition circuit. Without gas supply.

BY340-40 Fuego SCS

Accessories

BY344-06 Foot pedal. Accessory for BY340-40 Glass safety shield. For added safety when BY344-12

handling pathogenic material

BY344-27 Gas cartridge, CV360, 52g

Adapter for connecting BY344-27 to BY340-burners BY344-29

Note: Gas cartridges BY344-27 can be exported only as sea freight - deck cargo. Local purchase is recommended.

Lighters

Gas Lighter, Flint

Comprising spring holder, adjustable shielded flint and striking plate.

BY380-40 Gas lighter, flint

BY382-10 Spare flints, pack of 10

Gas Lighter, Piezo

Suitable for igniting the common fuel gases. Sparks produced by squeezing the handle. No battery required.

BY385-10 Gas lighter, piezo

Liquid Fuel Burner, Safety Pattern

For use with methylated spirit. Glass reservoir. With virtually leakproof, screw-on metal wick support, wick and metal screw cap cover.

BY400-16 100ml

Electric Heaters for test tubes, crucibles, instruments, etc. - see HE760 in the Heating section.

Wood splints - see GE350-10.



BY340-40 in use, BY340-30 is similar











