## **Filtration**

### **Membrane Filter Holders and Filtration System**

### Filter Holders, Vacuum, Glass

Borosilicate glass with metal clamp, stainless steel membrane support screen, PTFE gasket and rubber stopper to fit accessory manifolds. Supplied singly.

	For membrane dia. mm	Reservoir ml	
FC335-05	25	15	
FC335-09	47	300	
FC335-13	90	1000	

#### Filter Holders, Vacuum, Stainless Steel

All stainless steel construction for durability. Can be flame sterilised. With reservoir volume indicator mark and stopper to fit accessory manifolds. Supplied singly.

	For membrane dia. mm	Reservoir ml	
FC336-05	47	100	
FC336-09	47	300	
FC336-13	47	500	

# **Accessory Stainless Steel lids for FC336 holders only.** With vent. For funnels with reservoirs as indicated.

FC336-25	100ml
FC336-29	300ml
FC336-33	500ml

#### **Filter Manifolds**

Stainless steel. For use with FC335 and FC336 vacuum filter holders. With stopcock on each position. Supplied singly.

FC338-10	3 position
FC338-20	6 position

### **Waste Reservoirs**

Autoclavable, resistant plastic, waste reservoirs specifically designed for use with filtration manifolds. A removable lid with silicone 'O'-ring sealing gasket incorporates an overflow protection float valve and inlet/outlet tubing ferrules of diameters as indicated.

Capacity	ml	1200	3000
Construction		Polyethersulphone	Polycarbonate
Inlet/outlet ferrule o.d. n	nm	5	8

FC339-20	1200ml waste reservoir
FC339-30	3000ml waste reservoir



### FC335




FC336





FC338-10



FC338-20



FC339-20 FC339-30



